MONICON

IR80 CO2 GAS MONITOR

El Symaat El Him

Features

- Microprocessor based
- 4-20mA Analogue Output
- Voltage free relay contacts
- · RS485 digital interface
- Alphanumeric dot-matrix display

Usines Pharmaceurt

- · "Óne Person" calibration
- · Dual detectors
- Temperature compensation
- Standalone operation


The Monicon IR80 is a high quality, self contained, NDIR (Non Dispersive Infra Red) gas sensor that offers a host of sophisticated features to provide fast, reliable warnings against exposure to dangerous concentrations of carbon dioxide.

The IR80 will operate as a standalone instrument or in conjunction with a controller or a computer. It is housed in an attractive, compact enclosure and may be configured or calibrated by one person.

The gas concentration is indicated on a rugged 8character alphanumeric display which also indicates instrument status.

The IR80 is fully user programmable and no physical adjustments are necessary during calibration as the on-board computer assists the calibration procedure.

All user variables are stored in non-volatile memory (EEPROM) and retained indefinitely even during total power failure.





Typical Applications for the IR80

- · Breweries
- Landfill Sites
- Food processing
- Soft Drinks Manufacture
- Cellars
- Chemical Processing
- Ventilation Systems
- · Laboratories
- Mushroom Farming
- Greenhouses

The IR80 uses advanced NDIR technology combined with surface-mount microprocessor and firmware technology. A pulsed infrared source emits a broad spectrum infrared beam within an optical cavity. The system measures the adsorption of infrared energy as it passes through a gas sample. Different gases have clearly defined absorption characteristics, their concentration can be determined by their absorption of infrared radiation at the wavelength determined by filter lambda 1 in the diagram.

To compensate for interfering factors filter lambda 2 isolates another wavelength which is used to measure the total transmission through the optical cavity and is not affected by the gas being monitored. By comparing the infrared energy reaching each of the two detectors, the concentration of the gas sample can be determined. The signal processor compares and linearises these two signals. A thermistor monitors the sensor temperature and the signal processor factors in variations caused by temperature changes.

The unit is calibrated or user-programmed by means of on-board pushbutton switches. The operator is then guided through a variety of options by a userfriendly menu. The CPU constantly verifies system operation. In the unlikely event of a fault, the operator is alerted with a helpful diagnostic display.

IR80 Specifications

Supply voltage Power consumption **Circuit protection Transient Protection** Analogue output Analogue output load **Operating temperature** Storage temperature **Humidity range Preconditioning Requirements Full-Scale range** Response time (T90) Drift, S.T.P. continuous duty in air Linearity Repeatability Resolution Sensor MTBF **Recommended Calibration Interval** Weight **RS485** operating mode Max. units on RS485 loop **RS485** comm parameters RS485 error checking Unit interrogation time **Relay contacts Option setting** Alarm setting Alarm types **Recommended calibration flow rate** Mounting holes User variable storage Electromagnetic Conformance (EMC) Cable gland entry Terminations Enclosure

Literature supplied

Nominal 24Vdc (operates from 20Vdc to 35Vdc) 2W nominal, 2.3W maximum Electronic current limiter. 1.5A auto-reset PCB mounted, 3 Joule, Metal Oxide Varistor 4-20mA current source referenced to 0V 100 Ohms typical, 500 Ohms maximum -20°C to +50°C -40°C to +66°C 10%RH to 90%RH (Non-condensing) Operational: 30 seconds, Specification: 60 minutes 0 - 5% CO Typically <45 seconds <3% over three months ±5% ±2% 1% 10 years (calculations based on MIL-HDBK-217F) 12 months (depending on application) 1.5Kg (including sensor) Slave mode, half duplex, polled 100 1200-N-8-1 1 byte checksum 400mS SPST, NO, 230V @ 1A each for A1 & A2 Digital setting (all options fitted as standard and user selectable) Digital setting (fully adjustable between 10% and 90% of full scale) Energised/de-energised. Enrichment/deficiency. User selectable 500mL per minute 4 holes, diam 5mm, spaced 145mm horizontally, 63mm vertically Non-volatile RAM (EEPROM) Complies with EN50081 and EN50082 M20 x 1.5 Detatchable, PCB mounted terminal blocks to accept 1.5mm² cable Epoxy coated aluminium. Size W: 160mm H: 100mm D: 60mm

